



More information on the website  
[mirror.radwag.com/ja/info,w1,HA6](https://mirror.radwag.com/ja/info,w1,HA6)

## C315.4P.1500/3000.C パレット用はかり

WP-239-1000



The drawings, photos and graphics used are for illustrative purposes only.

### 機能



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit  
measurement



GLP Procedures



Animal weighing



ALIBI Memory

### データシート

#### 計測パラメータ

最大ひょう量 [Max]	1500 / 3000 kg
最小荷重	10 kg
最小表示 [d]	500 / 1000 g
法定計量時の単位 [e]	500 / 1000 g
風袋範囲	-3000 kg
OIMLクラス	III

物理的パラメータ	
ディスプレイ	4,3" LCD (ターミナル)
ケーブル長	3 m
計量皿寸法	840×1200 mm
デバイスの寸法 幅×奥行×高さ	1322×840×85 mm
梱包寸法 幅×奥行×高さ	1400×900×430 mm
インジケータ付きスケール質量	43 kg
工事中	
保護クラス	IP 65 ステンレススチール, IP 67 ステンレススチール, IP 43 円筒形
通信インターフェース	
通信インターフェース	RS232
オプションのインターフェース	RS232
電気的パラメータ	
電源	100 – 240 V AC 50/60 Hz バッテリー
消費電力 max.	5 W
バッテリー駆動時間	max 8h
環境条件	
動作温度	-10 – +40 °C
相対湿度	10% – 85% RH 温度における



Additional fee for verification



## アクセサリ (Additional Fee)

### 電源アダプタ

RS 232 ケーブル (はかり - プリンタ)  
 スタンド、壁取り付けキット、取り付けブラケット  
 シガーライターソケット電源ケーブル  
 ディスプレイ  
 RS 232、RS 485 ケーブル

### RS 232 – イーサネットコンバータ




AP2-1 電流ループユニット  
 RS 232 – USB コンバータ  
 RS 232 – RS 485 コンバータ  
 レシートプリンタ

## ソフトウェア (Additional Fee)

- RAD Key [WX-010-0005]
- Scale Editor 2.1 [WX-010-0173]

- R-Lab [WX-010-0080]

## デバイスの寸法 幅x奥行x高さ



Warunki transportu i przemieszczania wagi paletowej przy pomocy kółek jezdnych oraz uchwytów.

Transport of the pallet scale using casters and handles.