



More information on the website
mirror.radwag.com/us/info,w1,HOL

DWT/RC 150/HYF Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]		150 kg
Minimum load		1 kg
Readability [d]		50 g
Tare range		-150 kg
Physical parameters		
Display		10" graphic colour touchscreen
Weighing platform height		800 ± 50 mm (other levels of platform on client requirement)
Construction		
Protection class		IP 66 / 67
Operating temperature		-10 – +40 °C
Features of use		
Conveyor velocity		0,1 – 0,5 m/s



Accessories

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]