



More information on the website
mirror.radwag.com/us/info,w1,HYL

HX5.EX-1.150.H6 One Load Cell Platform Scale

WW-006-0043



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	150 kg
Minimum load	1 kg
Readability [d]	50 g
Verification unit [e]	50 g
Tare range	-150 kg
OIML Class	III

Physical parameters		
Display		5" graphic colour
Cable length		2,5 m
Weighing pan dimensions		800×800 mm
Packaging dimensions W x D x H		820×1250×490 mm
Net weight		46,8 kg
Gross weight		53 kg
Construction		
Protection class		IP 66 / 67 construction, IP 66 / 68 terminal
ATEX Certification		II 2G Ex ib IIB T4 Gb
IECEx Certification		Ex ib IIB T4 Gb
Construction		Stainless steel AISI304
Weighing pan material		Stainless steel AISI304
Communication interface		
Communication interface		2×RS232, RS485
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz
Power consumption max.		15 W
Environmental conditions		
Operating temperature		-10 – +40 °C
Relative humidity		10% – 85% RH no condensation
Indicator		PUE HX5.EX-1



Additional fee for verification



Accessories (Additional Fee)

Communication modules
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
Weighing Terminal

Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]