



More information on the website  
[mirror.radwag.com/ja/info,w1,l25](http://mirror.radwag.com/ja/info,w1,l25)

# MAS 220

WX-016-0066



The drawings, photos and graphics used are for illustrative purposes only.

## Table of Specifications

Maximum weighing capacity	
Maximum [Max]	220 g
Minimum	10 mg
Internal calibration weight	22 g
Resolution [d]	0,1 mg
Capacity	-220 g
Capacity	0,1 mg
Capacity	±0,2 mg
Capacity	3,5 s
Capacity	Stainless steel (304)
Capacity	
Capacity	IP 32
Capacity	Stainless steel
Capacity	
Capacity	RS232, USB-B

<p>⚙️</p>	
⚡	100 – 240 V AC 50/60 Hz
<p>🌡️</p>	
🌡️	+10 – +40 °C
💧	40% – 80%
<p>📏</p>	
📏	ø42 mm
📏	175×236×105 mm
📏	515×340×295 mm
📏	3 kg



### 🔌 (Additional Fee)

🔌  
 🔌  
 RS 232 🔌 RS 485 🔌

RS 232 – USB 🔌  
 RS 232 🔌 (🔌 - 🔌)

### 🔌 (Additional Fee)

- [WX-010-0005]
- [WX-010-0080]

- [WX-010-0187]
- [WX-010-0104]

🔌

