




More information on the website  
[mirror.radwag.com/us/info,w1,l70](https://mirror.radwag.com/us/info,w1,l70)

# H315.4N.1500.H4.LD Stainless Steel Ramp Scale

WP-234-0026



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit  
measurement



Animal weighing

## Datasheet

| Maximum capacity [Max]                 | 1500 kg            |
|----------------------------------------|--------------------|
| Minimum load                           | 10 kg              |
| Readability [d]                        | 500 g              |
| Verification unit [e]                  | 500 g              |
| Tare range                             | -1500 kg           |
| Max readability for non-verified scale | 200 g              |
| OIML Class                             | III                |
| Physical parameters                    |                    |
| Display                                | 4,3" LCD (backlit) |

| Physical parameters            |                                                                 |
|--------------------------------|-----------------------------------------------------------------|
| Cable length                   | 3 m                                                             |
| Weighing pan dimensions        | 1500×1500 mm                                                    |
| Packaging dimensions W x D x H | 2040×1900×580 mm                                                |
| Net weight                     | 280 kg                                                          |
| Gross weight                   | 450 kg                                                          |
| Construction                   |                                                                 |
| Protection class               | IP 66 / 69 construction, IP 66 / 67 / 69 terminal               |
| Communication interface        | RS232, USB                                                      |
| Optional interfaces            | RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA |
| Power supply                   | 100 – 240 V AC 50/60 Hz                                         |
| Optional power supply          | internal rechargeable battery                                   |
| Operation time on batteries    | max 7h                                                          |
| Operating temperature          | -10 – +40 °C                                                    |
| Relative humidity              | 10% – 85% RH no condensation                                    |



Additional fee for verification



## Accessories (Additional Fee)

AP2-3 Current Loop Unit  
 RS 232 cables (scale - printer)  
 Displays  
 Ethernet cables (scale - Ethernet)  
 RS 232, RS 485 cables  
 Power Adapters


RS 232 – Ethernet Converter  
 USB adapter  
 Receipt Printer  
 USB cable (scale - printer)  
 Stands, wall mounting kits and mounting brackets  
 RS 232 – USB Converter

## Software (Additional Fee)

• RAD Key [WX-010-0005]

• Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions W x D x H



|                    | A [mm] | B [mm] | C [mm] | D [mm] |
|--------------------|--------|--------|--------|--------|
| H315.4N.150.H1.LD  | 840    | 860    | 45     | 426    |
| H315.4N.300.H1.LD  | 840    | 860    | 45     | 426    |
| H315.4N.600.H1.LD  | 840    | 860    | 45     | 426    |
| H315.4N.150.H2.LD  | 1100   | 1200   | 45     | 426    |
| H315.4N.300.H2.LD  | 1100   | 1200   | 45     | 426    |
| H315.4N.600.H2.LD  | 1100   | 1200   | 45     | 426    |
| H315.4N.300.H3.LD  | 1200   | 1500   | 45     | 426    |
| H315.4N.600.H3.LD  | 1200   | 1500   | 45     | 426    |
| H315.4N.1500.H2.LD | 1100   | 1200   | 52     | 476    |
| H315.4N.1500.H3.LD | 1200   | 1500   | 52     | 476    |
| H315.4N.300.H4.LD  | 1500   | 1500   | 52     | 476    |
| H315.4N.600.H4.LD  | 1500   | 1500   | 52     | 476    |
| H315.4N.1500.H4.LD | 1500   | 1500   | 52     | 476    |