



More information on the website  
[mirror.radwag.com/us/info,w1,I9C](http://mirror.radwag.com/us/info,w1,I9C)

# CY10.1,5.F1.K.M3 Multifunctional Scale

WP-125-0007



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	1,5 kg
Minimum load	10 g
Readability [d]	0,5 g
Verification unit [e]	0,5 g
Tare range	-1,5 kg
Max readability for non-verified scale	0,05 g
Stabilization time	2 s

Metrological parameters	
Adjustment	external
OIML Class	III
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	1 m
Weighing pan dimensions	300×300 mm
Packaging dimensions W x D x H	570×390×170 mm
Net weight	6,3 kg
Gross weight	7,1 kg
Construction	
Protection class	IP 65 construction, IP 43 terminal
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10–19W*
Environmental conditions	
Operating temperature	-10 – +40 °C
Storage temperature	-25 – +70 °C
Multiple range	YES
Features of use	
Max number of platforms	max.2

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



## Accessories (Additional Fee)

### MediaBox

Mild steel powder coated weighing platforms  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module  
Additional modules  
Platforms in plastic casing  
Protective cover for balances

### Barcode scanners

Label Printers  
RS 232, RS 485 cables  
Stands, wall mounting kits and mounting brackets  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions W x D x H

