



More information on the website
mirror.radwag.com/br/info,w1,IOH

Balança WPY 1,5/3.D2.CPE

WK-308-1002



The drawings, photos and graphics used are for illustrative purposes only.

Funções



Dosing



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Peak hold



Formulation


Newton unit
measurement


Statistics



Checkweighing



IR sensors



Animal weighing



Differential weighing



Packaged Goods Control



ALIBI Memory

Ficha Técnica

Parâmetros metrológicos

Capacidade máxima [máx]	1,5 / 3 kg
Carga mínima	10 / 20 g
Resolução [d]	0,5 / 1 g
Unidade de verificação [e]	0,5 / 1 g
Faixa de tara	-3 kg
Classe OIML	III

Parâmetros físicos	
Display	Tela touchscreen colorida resistiva de 5,7"
Comprimento até cabo	1 m
Dimensões até prato de pesagem	195×195 mm
Dimensões da embalagem L x P x A	530×310×150 mm
Dimensões da embalagem L x P x A	530×310×150 mm
Dimensões da embalagem L x P x A	530×310×150 mm
Construção	
Classe de proteção	IP 43
Interface de comunicação	
Interface de comunicação	2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Parâmetros elétricos	
Fonte de alimentação	100 – 240 V AC 50/60 Hz
Condições ambientais	
Temperatura de operação	-10 – +40 °C
Umidade relativa	10% – 85% RH sem condensação

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Acessórios (Additional Fee)

Leitores de cartão transponder
 Adaptadores de energia
 Cabos de alimentação para acendedor de cigarro automotivo
 !Leitores de código de barras
 RS 232, RS 485 cabos
 Impressoras de etiquetas
 Displays

Cabos IN/OUT
 Teclado, interruptores externos
 Impressora de recibos
 Pesos padrão F1 -
 pesos botão sem câmara de ajuste, conjuntos
 Módulo de plataformas de pesagem adicionais
 RS 232 – Conversor USB
 Cabos RS 232 (plataforma - impressora)

Software (Additional Fee)

- E2R Pesagem [WX-010-0099]
- Leitor Audit Trail [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Editor de etiquetas R02 [WX-010-0094]
- R-Lab [WX-010-0080]