




More information on the website  
[mirror.radwag.com/en/info,w1,IOH](http://mirror.radwag.com/en/info,w1,IOH)

# WPY 1,5/3.D2.PGC Scale

WK-308-1002



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Dosing
-  Labelling
-  Plus/Minus Control
-  Percent Weighing
-  Totalizing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Animal weighing
-  Differential weighing
-  Packaged Goods Control
-  ALIBI Memory

## Datasheet

| Metrological parameters |            |
|-------------------------|------------|
| Maximum capacity [Max]  | 1.5 / 3 kg |
| Minimum load            | 10 / 20 g  |
| Readability [d]         | 0.5 / 1 g  |
| Verification unit [e]   | 0.5 / 1 g  |
| Tare range              | -3 kg      |
| OIML Class              | III        |

| Physical parameters            |   |
|--------------------------------|---|
| Display                        | 5.7" resistive colour touchscreen                         |
| Cable length                   | 1 m   |
| Weighing pan dimensions        | 195×195 mm  |
| Packaging dimensions W x D x H | 530×310×150 mm  |
| Packaging dimensions W x D x H | 530×310×150 mm  |
| Packaging dimensions W x D x H | 530×310×150 mm  |
| Construction                   |   |
| Protection class               | IP 43   |
| Communication interface        |   |
| Communication interface        | 2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi |
| Electrical parameters          |   |
| Power supply                   | 100 – 240 V AC 50/60 Hz                                   |
| Environmental conditions       |   |
| Operating temperature          | -10 – +40 °C  |
| Relative humidity              | 10% – 85% RH no condensation                              |

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Transponder card readers  
 Power Adapters  
 RS 232 cables (scale - printer)  
 Cigarette lighter receptacle power supply cables  
 Barcode scanners  
 RS 232, RS 485 cables  
 Label Printers  
 Displays

IN/OUT Cables  
 Keypad, external switches  
 Stands, wall mounting kits and mounting brackets  
 Receipt Printer  
 F1 Mass Standard -  
 knob weights without adjustment chamber, set  
 Additional Weighing platforms Module  
 RS 232 – USB Converter

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Audit Trail Reader [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]