



More information on the website  
[mirror.radwag.com/us/info,w1,IWP](http://mirror.radwag.com/us/info,w1,IWP)

# IM01.EX-4/3 Communication Module

WX-016-0173



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Construction                                      |                                                   |
|---------------------------------------------------|---------------------------------------------------|
| Protection class                                  | IP 66 / 68 (1,5m)                                 |
| ATEX Certification                                | II (2)G [Ex ib] IIC Gb<br>II (2)D [Ex ib] IIIC Db |
| Housing                                           | aluminum                                          |
| Communication interface                           |                                                   |
| 2×RS232, USB, 12IN / 12OUT, Ethernet, Profibus DP |                                                   |
| Power supply                                      |                                                   |
| 100 – 240 V AC 50/60 Hz                           |                                                   |
| Power consumption max.                            |                                                   |
| 10 W                                              |                                                   |
| Operating temperature                             |                                                   |
| -10 – +40 °C                                      |                                                   |
| Storage temperature                               |                                                   |
| -20 – +60 °C                                      |                                                   |
| Relative humidity                                 |                                                   |
| 10% – 85% RH no condensation                      |                                                   |
| Physical parameters                               |                                                   |
| Device dimensions W x D x H                       | 222×146×81 mm                                     |
| Net weight                                        | 1,9 kg                                            |

## Physical parameters

Gross weight

2,5 kg





## Compatible with (Additional Fee)

HX5.EX-1.4P2 H Stainless steel Beam Scales  
HX5.EX-1 HR Stainless Steel 1-Load-Cell Platform Scales  
RS 232 cables (scale - printer)  
HX5.EX-1.4P2 C Beam Scales  
HX5.EX-1.4N Stainless Steel Ramp Scales  
HX5.EX-1.4 C 4-Load-Cell Platform Scales  
HX5.EX-1.4P H Stainless steel pallet scales  
HX5.EX-1.4 H/Z Stainless steel platform scales, pit version  
HX5.EX-1 C 1 Load Cell Platform Scales

HX5.EX-1 H Waterproof Platform Scales  
PUE HX5.EX Weighing Terminal  
HX5.EX-1.4 H Stainless Steel 4-Load-Cell Platform Scales  
RS 232, RS 485 cables  
IN/OUT Cables  
HX5.EX-1.4P C Pallet scales  
USB adapter  
USB cable (scale - printer)  
RS 232 – USB Converter

## Device dimensions W x D x H



IM01.EX