



UMA 100.5Y Automatic Mass Comparator

WL-415-0005

More information on the website
mirror.radwag.com/us/info,w1,lXE



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E0 Calibration Range	1 – 100 * g
E1 Calibration Range	1 – 100 g
E2 Calibration Range	1 – 100 g
F1 Calibration Range	1 – 100 g
F2 Calibration Range	1 – 100 g
M1 Calibration Range	1 – 100 g
M2 Calibration Range	1 – 100 g
Maximum capacity [Max]	110 g
Readability [d]	0,001 mg
Standard repeatability [5% Max]	1,5 µg
Standard repeatability [Max]	2 µg
Permissible repeatability	3,5 µg
Linearity	±10 µg
Eccentricity (tested load)	0 mg
Electric compensation range	-1 g – +10 g
Stabilization time	30 s

Adjustment	internal (automatic)
Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	∅21 mm
Weighing device dimensions	700×585×720 mm
Controlling device dimensions	460×250×195 mm
Packaging dimensions W x D x H	1200×1000×1566 mm
Net weight	114,3 kg
Gross weight	204,3 kg
Construction	
Supplementary weights	internal (automatic)
Supplementary weights external	-
Magazine	36
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0,5 °C / 12 h (±0,3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (3% / 4 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

RFID Tags
 Antivibration tables
 Additional modules
 Protective cover for balances
 Barcode scanners


RS 232, RS 485 cables
 THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232 cables (scale - printer)

Software (Additional Fee)

• RAD Key [WX-010-0005]
 • RMCS System Network Management of Calibration Process [WX-010-0048]

• RMCS Lite [WX-010-0164]


Device dimensions W x D x H



UMA-100, UMA-1000



UMA-control unit



UMA-5