



More information on the website  
[mirror.radwag.com/en/info,w1,lz4](http://mirror.radwag.com/en/info,w1,lz4)

# PL/60/H4 Platform

WX-009-0016



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters |                         |
|-------------------------|-------------------------|
| Maximum capacity [Max]  | 60 kg                   |
| Readability [d]         | 20 g                    |
| Construction            |                         |
| Protection class        | IP 68                   |
| Construction            | Stainless steel AISI304 |
| Weighing pan material   | Stainless steel AISI304 |
| Physical parameters     |                         |
| Weighing pan dimensions | 500×500 mm              |
| Packaging dimensions    | 610×610×330 mm          |

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.



## Accessories (Additional Fee)

PUE 5 Weighing Terminal  
 PUE 7.1 Weighing Terminal  
 PUE HX7 Weighing Terminal

PUE C315 Weighing Terminal  
 PUE HY10 Weighing Terminal  
 PUE H315 Weighing Terminal


## Device dimensions




PL/D2



PLC/F1



PLC/C2  
PLC/C3



PL/H  
PL/HR



| Platform type       | A1  | A2  | H     |
|---------------------|-----|-----|-------|
| PL/D2               | 238 | 216 | 82±3  |
| PLC/F1              | 300 | 300 | 70±3  |
| PLC/C2              | 402 | 502 | 103±3 |
| PLC/C3              | 701 | 501 | 130±5 |
| PL/H1 / PL/HR1      | 150 | 200 | 85±3  |
| PL/H2 / PL/HR2      | 250 | 300 | 103±3 |
| PL/H3 / PL/HR/3     | 410 | 410 | 98±3  |
| PL/H3/5 / PL/HR/3/5 | 400 | 600 | 155±3 |
| PL/H4 / PL/HR/4     | 500 | 500 | 155±3 |
| PL/H5 / PL/HR/5     | 600 | 600 | 155±3 |
| PL/H6               | 800 | 800 | 135±3 |

dimensions in mm