



More information on the website
mirror.radwag.com/en/info,w1,JEQ

P0261 Cable

WX-013-0010



The drawings, photos and graphics used are for illustrative purposes only.

Overview

RS 232 cable for connecting a balance/scale (PUE H315 indicator) to an Epson printer.

Standard cable length: 2m Customized cable length (extra charge): 5 or 10m

Compatible with:

Scales operated by means of PUE H315 indicator Scales operated by means of PUE H315/Z indicator PUE H315 indicator PUE H315/Z indicator

Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale
 H315 4H Stainless Steel Platform Scale
 H315 4P2.H Stainless steel Beam Scales
 H315 H Waterproof Platform Scale
 H315.4 H/Z Stainless Steel Platform Scale, pit version
 H315 4N.H Stainless Steel Ramp Scale
 H315 4N.H.LD Stainless Steel Ramp Scale

H315 2K Overhead Track Scales
 H315 4P.H Stainless Steel Pallet Scales
 H315 4I.S Livestock Scales
 H315 4I.H Stainless Steel Livestock Scales
 H315 Stainless Steel Overhead Track Scales
 Receipt Printer