



More information on the website
mirror.radwag.com/ja/info,w1,JEQ

P0261

WX-013-0010



The drawings, photos and graphics used are for illustrative purposes only.

☒☒

RS232 PUE H315 / Epson

Length: 2m 5m 10m

Notes:

PUE H315 PUE H315/Z PUE H315 PUE H315/Z

☒☒☒☒ (Additional Fee)

- H315 HR
- H315 4H
- H315 4P2.H
- H315 H
- H315.4 H/Z
- H315 4N.H
- H315 4N.H.LD

- H315 2K
- H315 4P.H
- H315 4I.S
- H315 4I.H
- H315