

P0261 Cable

WX-013-0010



mirror.radwag.com/us/info,w1,JEQ



The drawings, photos and graphics used are for illustrative purposes only.

Overview

RS 232 cable for connecting a balance/scale (PUE H315 indicator) to an Epson printer.

Standard cable length: 2m

Customized cable length (extra charge): 5 or 10m

Compatible with:

- Scales operated by means of PUE H315 indicator
- Scales operated by means of PUE H315/Z indicator
- PUE H315 indicator
- PUE H315/Z indicator

Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale H315 4H Stainless Steel Platform Scale H315 4P2.H Stainless steel Beam Scales H315 H Waterproof Platform Scale H315.4 H/Z Stainless Steel Platform Scales, pit version H315 4N.H Stainless Steel Ramp Scale H315 4N.H.LD Stainless Steel Ramp Scale

H315 2K Overhead Track Scales H315 4P.H Stainless Steel Pallet Scales H315 4I.S livestock scales H315 4I.H Stainless steel livestock scales H315 Stainless steel overhead track scales Receipt Printer