



More information on the website  
[mirror.radwag.com/us/info,w1,JEQ](https://mirror.radwag.com/us/info,w1,JEQ)

## P0261 Cable

WX-013-0010



The drawings, photos and graphics used are for illustrative purposes only.

### Overview

RS 232 cable for connecting a balance/scale (PUE H315 indicator) to an Epson printer.

Standard cable length: 2m

Customized cable length (extra charge): 5 or 10m

Compatible with:

- Scales operated by means of PUE H315 indicator
- Scales operated by means of PUE H315/Z indicator
- PUE H315 indicator
- PUE H315/Z indicator

### Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale  
 H315 4H Stainless Steel Platform Scale  
 H315 4P2.H Stainless steel Beam Scales  
 H315 H Waterproof Platform Scale  
 H315.4 H/Z Stainless Steel Platform Scales, pit version  
 H315 4N.H Stainless Steel Ramp Scale  
 H315 4N.H.LD Stainless Steel Ramp Scale

H315 2K Overhead Track Scales  
 H315 4P.H Stainless Steel Pallet Scales  
 H315 4I.S livestock scales  
 H315 4I.H Stainless steel livestock scales  
 H315 Stainless steel overhead track scales  
 Receipt Printer