



More information on the website
mirror.radwag.com/en/info,w1,JFA

Internal battery (PUE H315)

WX-008-0213



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Physical parameters	
Voltage	7.2 V
Capacity	2000 mAh
Device dimensions	152×29×14.5 mm
Net weight	28 g
Environmental conditions	
Operating temperature	0 – +40 °C



Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale
 H315 4H Stainless Steel Platform Scale
 H315 4P2.H Stainless steel Beam Scales
 H315 H Waterproof Platform Scale
 H315.4 H/Z Stainless Steel Platform Scale, pit version

H315 4C Platform Scale
 H315 2K Overhead Track Scales
 H315 4P.H Stainless Steel Pallet Scales
 H315 4I.S Livestock Scales
 H315 4I.H Stainless Steel Livestock Scales

H315 4N.H Stainless Steel Ramp Scale
H315 4N.H.LD Stainless Steel Ramp Scale

PUE H315 Weighing Terminal
H315 Stainless Steel Overhead Track Scales