



More information on the website  
[mirror.radwag.com/ja/info,w1,JFA](http://mirror.radwag.com/ja/info,w1,JFA)

## ⓧⓧⓧⓧⓧⓧ (PUE H315)

WX-008-0213



The drawings, photos and graphics used are for illustrative purposes only.

### ⓧⓧⓧⓧⓧⓧ

ⓧⓧⓧⓧⓧⓧ	
ⓧⓧ	7,2 V
ⓧⓧⓧ	2000 mAh
ⓧⓧⓧⓧⓧⓧ	152×29×14,5 mm
ⓧⓧⓧ	28 g
ⓧⓧⓧ	
ⓧⓧⓧ	0 – +40 °C



### ⓧⓧⓧⓧ (Additional Fee)

H315 HR ⓧⓧⓧⓧⓧⓧⓧⓧⓧ  
 H315 4H ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ  
 H315 4P2.H ⓧⓧⓧⓧⓧⓧⓧⓧⓧ  
 H315 H ⓧⓧⓧⓧⓧⓧⓧⓧⓧ  
 H315.4 H/Z ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ

H315 4C ⓧⓧⓧⓧⓧⓧⓧⓧⓧ  
 H315 2K ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ  
 H315 4P.H ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ  
 H315 4I.S ⓧⓧⓧⓧⓧ  
 H315 4I.H ⓧⓧⓧⓧⓧⓧⓧⓧⓧ

H315 4N.H  
H315 4N.H.LD

PUE H315  
H315