



More information on the website
mirror.radwag.com/us/info,w1,JFA

Internal battery (PUE H315)

WX-008-0213



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Physical parameters	
Voltage	7,2 V
Capacity	2000 mAh
Device dimensions W x D x H	152×29×14,5 mm
Net weight	28 g
Environmental conditions	
Operating temperature	0 – +40 °C



Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale
 H315 4H Stainless Steel Platform Scale
 H315 4P2.H Stainless steel Beam Scales
 H315 H Waterproof Platform Scale
 H315.4 H/Z Stainless Steel Platform Scales, pit version

H315 4N.H.LD Stainless Steel Ramp Scale
 H315 4C Platform Scale
 H315 2K Overhead Track Scales
 H315 4P.H Stainless Steel Pallet Scales
 PUE H315 Terminal

