



More information on the website  
[mirror.radwag.com/en/info,w1,JFT](https://mirror.radwag.com/en/info,w1,JFT)

# DWT/RC 30/HYF Checkweigher

WK-106-0014



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                                                              |
|--------------------------|--------------------------------------------------------------|
| Maximum capacity [Max]   | 30 kg                                                        |
| Minimum load             | 200 g                                                        |
| Readability [d]          | 10 g                                                         |
| Tare range               | -30 kg                                                       |
| Physical parameters      |                                                              |
| Display                  | 10.1" graphic colour touchscreen                             |
| Weighing platform height | 800 ± 50 mm (other levels of platform on client requirement) |
| Construction             |                                                              |
| Protection class         | IP 66 / 67                                                   |
| Environmental conditions |                                                              |
| Operating temperature    | -10 – +40 °C                                                 |
| Features of use          |                                                              |
| Conveyor velocity        | 0.1 – 0.5 m/s                                                |



## Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]