



More information on the website  
[mirror.radwag.com/us/info,w1,JFT](http://mirror.radwag.com/us/info,w1,JFT)

# DWT/RC 30/HYF Checkweigher

WK-106-0014



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	30 kg
Minimum load	200 g
Readability [d]	10 g
Tare range	-30 kg
<b>Physical parameters</b>	
Display	10" graphic colour touchscreen
Weighing platform height	800 ± 50 mm (other levels of platform on client requirement)
<b>Construction</b>	
Protection class	IP 66 / 67
Operating temperature	-10 – +40 °C
<b>Features of use</b>	
Conveyor velocity	0,1 – 0,5 m/s



## Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]