



More information on the website
mirror.radwag.com/en/info,w1,JKU

HX7.4P2.1500.H Stainless Steel Multifunctional Beam Scale

WP-229-0011



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Formulation



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 kg
Minimum load	10 kg
Readability [d]	500 g
Verification unit [e]	500 g
Tare range	-1500 kg
Max readability for non-verified scale	500 g
OIML Class	III

Physical parameters	
Display	7" graphic colour
Cable length	3 m + 5 m
Weighing pan dimensions	2 pcs 1.2 m
Device dimensions W x D x H	1200×120×85 mm
Packaging dimensions W x D x H	1400×400×550 mm
Net weight	39.7 kg
Gross weight	55.3 kg
Construction	
Protection class	IP 66 / 69 construction, IP 66 / 67 terminal
Keypad	membrane
Construction	Stainless steel AISI304
Communication interface	
Communication interface	RS232, USB-A, 4IN, 4OUT, Ethernet, Modbus RTU
Optional interfaces	USB (M12 4P), Ethernet, module RS485, module RS232, module Profibus (Dp SLAVE), PROFINET (RRJ45), EtherNet/IP (RRJ45), 12 IN, 12 OUT, 4-20mA, 0-10V
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	25 W
Optional power supply	12 – 24 V DC
Environmental conditions	
Operating temperature	-10 – +40 °C
Storage temperature	-10 – +50 °C
Relative humidity	10% – 80% RH no condensation
Indicator	PUE HX7
Number of buttons	22
Features of use	
Max number of platforms	2



Additional fee for verification



Accessories (Additional Fee)


AP2-4 Current Loop Unit
 RS 232 cables (scale - printer)
 RS 232 cables (scale - ZEBRA printer)
 Displays
 Power Adapters
 RS 232, RS 485 cables
 USB cable (scale - printer)
 IN/OUT Cables
 Barcode scanners

Label Printers
 Stands, wall mounting kits and mounting brackets
 Keypad, external switches
 USB adapter
 Receipt Printer
 Additional Weighing platforms Module
 RS 232 – USB Converter
 Additional modules

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]
- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions W x D x H



	A	B	C	D
HX7.4P2.600.H	120	1200	85	1100
HX7.4P2.1500.H	120	1200	85	1100
HX7.4P2.3000.H	120	1200	85	1100
HX7.4P2.2000.H1	120	2000	105	1900
HX7.4P2.2000.H2	120	2500	105	2400
HX7.4P2.4000.H1	120	2000	155	1880
HX7.4P2.4000.H2	120	2500	155	2380
HX7.4P2.6000.H1	120	2000	155	1880
HX7.4P2.6000.H2	120	2500	155	2380