



More information on the website  
[mirror.radwag.com/en/info,w1,JM1](http://mirror.radwag.com/en/info,w1,JM1)

## MD 07 Metal Detector

WX-018-0002



The drawings, photos and graphics used are for illustrative purposes only.

### Overview

Closed, rectangular tunnel equipped with integrated electronic system. To be installed on band conveyors.

Industry:

- ☒ Food,
- ☒ Cosmetic,
- ☒ Chemical and pharmaceutical,
- ☒ Others.

Functionality: Product quality control, Reliable detection, Complete monitoring of the production line, Customer protection, Machine protection.

Main advantages: Compact design, Advanced contamination detection system, Easy and comfortable to use menu, Touch panel, Possibility of remote operation, Possibility of connecting a warning system or contamination separation system.

Optional equipment: Test cards - ball (balls) melted in plastic, used for sensitivity checking (numerous types and diameters – with certificates, if needed), Signalling device – sound and light signals, Printer: with RS 232 port (maximal cable length 100 meters), with RS 485 port (maximal cable length 1200 meters). Integrated IT solutions: mesuset (detector operation via laptop), mesunet (web integration and remote operating), others. Voltage control system: magnetic stabilizer, electronic stabilizer. Remote deleting switch-key. Transmission and mechanical separation systems solutions, Recoil system: lateral actuator system, trigger flap system, tape stranding device, others. Markers: pressure paint nozzle marking system, sack marker, others. Belt conveyor flight operating: “maneuverable” belt conveyor flight, others.

## **Compatible with (Additional Fee)**

DWM H2 Checkweighers

DWM Checkweighers