



More information on the website
mirror.radwag.com/en/info,w1,JM1

MD 07 Metal Detector



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Closed, rectangular tunnel equipped with integrated electronic system. To be installed on band conveyors.

Industry:

- Food;
- Cosmetic;
- Chemical and pharmaceutical;
- Others.

Use:

- Quality control;
- Customer protection;
- Machine protection.

Main advantages:

- Compact look;
- Easy and comfortable to use menu;
- Touch panel.

Optional equipment:

- Test cards - ball (balls) melted in plastic, used for sensitivity checking (numerous types and diameters – with certificates, if needed);
- Signalling device – sound and light signals;
- Printer:
 - with RS 232 port (maximal cable length 100 meters);
 - with RS 485 port (maximal cable length 1200 meters);
- Integrated IT solutions:
 - mesuset (detector operation via laptop);
 - mesunet (web integration and remote operating);
 - others;
- Voltage control system:
 - magnetic stabilizer;
 - electronic stabilizer;
- Remote deleting switch-key;
- Transmission and mechanical separation systems solutions;
- Recoil system:
 - lateral actuator system;
 - trigger flap system;
 - tape stranding device;
 - others;
- Markers:
 - pressure paint nozzle marking system;
 - sack marker;
 - others;
- Belt conveyor flight operating:
 - “maneuverable” belt conveyor flight;
 - others.

Compatible with

DWM H2 Checkweighers

DWM Checkweighers