



More information on the website  
[mirror.radwag.com/en/info,w1,JM1](https://mirror.radwag.com/en/info,w1,JM1)

## MD 07 Metal Detector



The drawings, photos and graphics used are for illustrative purposes only.

### Overview

Closed, rectangular tunnel equipped with integrated electronic system. To be installed on band conveyors.

#### Industry:

- Food;
- Cosmetic;
- Chemical and pharmaceutical;
- Others.

#### Use:

- Quality control;
- Customer protection;
- Machine protection.

#### Main advantages:

- Compact look;
- Easy and comfortable to use menu;
- Touch panel.

#### Optional equipment:

- Test cards - ball (balls) melted in plastic, used for sensitivity checking (numerous types and diameters – with certificates, if needed);
- Signalling device – sound and light signals;
- Printer:
  - with RS 232 port (maximal cable length 100 meters);
  - with RS 485 port (maximal cable length 1200 meters);
- Integrated IT solutions:
  - mesuset (detector operation via laptop);
  - mesunet (web integration and remote operating);
  - others;
- Voltage control system:
  - magnetic stabilizer;
  - electronic stabilizer;
- Remote deleting switch-key;
- Transmission and mechanical separation systems solutions;
- Recoil system:
  - lateral actuator system;
  - trigger flap system;
  - tape stranding device;
  - others;
- Markers:
  - pressure paint nozzle marking system;
  - sack marker;
  - others;
- Belt conveyor flight operating:
  - “maneuverable” belt conveyor flight;
  - others.

## Compatible with

DWM H2 Checkweighers

DWM Checkweighers