



More information on the website
mirror.radwag.com/en/info,w1,JM1

MD 07 Metal Detector

WX-018-0002



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Closed, rectangular tunnel equipped with integrated electronic system. To be installed on band conveyors.

Industry:

- Food;
- Cosmetic;
- Chemical and pharmaceutical;
- Others.

Use:

- Quality control;
- Customer protection;
- Machine protection.

Main advantages:

- Compact look;
- Easy and comfortable to use menu;
- Touch panel.

Optional equipment:

- Test cards - ball (balls) melted in plastic, used for sensitivity checking (numerous types and diameters – with certificates, if needed);
- Signalling device – sound and light signals;
- Printer:
 - with RS 232 port (maximal cable length 100 meters);
 - with RS 485 port (maximal cable length 1200 meters);
- Integrated IT solutions:
 - mesuset (detector operation via laptop);
 - mesunet (web integration and remote operating);
 - others;
- Voltage control system:
 - magnetic stabilizer;
 - electronic stabilizer;
- Remote deleting switch-key;
- Transmission and mechanical separation systems solutions;
- Recoil system:
 - lateral actuator system;
 - trigger flap system;
 - tape stranding device;
 - others;
- Markers:
 - pressure paint nozzle marking system;
 - sack marker;
 - others;
- Belt conveyor flight operating:
 - “maneuverable” belt conveyor flight;
 - others.

Compatible with (Additional Fee)

DWM H2 Checkweighers

DWM Checkweighers