



More information on the website
mirror.radwag.com/us/info,w1,JMK

MAS.80.R2 Weighing Module

WX-016-0355



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	80 g
Preload range	8 g
Readability [d]	0,01 mg
Repeatability	0,04 mg
Linearity	±0,05 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	internal
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	Stainless steel
Communication interface	RS232
Power supply	Adapter: 100 – 240V AC 50/60Hz; 12V DC 1,2A Module: 12V DC

Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
Physical parameters	
Weighing pan dimensions	ø56 mm
Device dimensions W x D x H	231x115x120 mm
Net weight	1,6 kg



Accessories (Additional Fee)

Antivibration tables	RS 232, RS 485 cables
R Terminal (WDM-8)	

Software (Additional Fee)

- R Panel [WX-010-0187]