



More information on the website
mirror.radwag.com/it/info,w1,K57

MPS 6000.Y Modulo di pesatura

WX-016-0071



The drawings, photos and graphics used are for illustrative purposes only.

Specifiche

Parametri metrologici	
Portata massima [Max]	6000 g
Divisione [d]	10 mg
Campo di tara	-6000 g
Parametri fisici	
Display	5,7" Resistive Color Touchscreen
Dimensione piatto	ø115 mm
Device dimensions	293×190×112 mm
Dimensioni del pacco	515×340×295 mm
Peso net	4,8 kg
Parametri elettrici	
Alimentatore	100 – 240 V AC 50/60 Hz
Environmental conditions	
Ambiente di lavoro	+15 – +35 °C
Umidità relativa	40% – 80%



Accessori (Additional Fee)

Tavoli antivibranti
 Tavolo di pesata professionale
 Cavo seriale RS 232, RS 485



RS 232 – USB Converter
 Cavo seriale RS 232 (connessione bilance - Stampanti)

Software (Additional Fee)


- RAD Key [WX-010-0005]
- R-LAB [WX-010-0080]

- R Panel [WX-010-0187]
- Software „Development Studio” RADWAG [WX-010-0104]


Device dimensions



MPS



R operator panel



Y operator panel