



More information on the website  
[mirror.radwag.com/us/info,w1,KRZ](https://mirror.radwag.com/us/info,w1,KRZ)

# SAL / C – Anti-vibration table in mild steel technology

WX-001-0076



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Construction	
Construction	mild steel St3S
Load-bearing capacity	40 kg
Physical parameters	
Packaging dimensions W x D x H	820×711×816 mm
Net weight	61 kg
Gross weight	72,5 kg
Length	770 mm
Width	680 mm
Height	815±10 mm



## Compatible with (Additional Fee)

MA X7.IC.A Moisture Analyzer  
MA 5Y Moisture Analyzer  
AS X7 Analytical Balance  
PS R2 Precision Balance  
WLC X7 Precision balance  
C32.PM Precision Balance  
MA X7.A Moisture Analyzer  
MA 5Y.IC Moisture Analyzer

MA R Moisture Analyzer  
PS R2.H Precision Balance  
Analytical Balance for Filters XA 5Y.F  
PS X7 Precision Balance  
PS R1 Precision Balance  
AS R2 PLUS Analytical Balance  
AS R1 PLUS Analytical Balance  
MAS.1.Y Modules

## Device dimensions W x D x H

