



More information on the website
mirror.radwag.com/us/info,w1,KRZ

SAL / C – Anti-vibration table in mild steel technology

WX-001-0076



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Construction	
Construction	mild steel St3S
Load-bearing capacity	40 kg
Physical parameters	
Packaging dimensions W x D x H	820×711×816 mm
Net weight	61 kg
Gross weight	72,5 kg
Length	770 mm
Width	680 mm
Height	815±10 mm

Compatible with (Additional Fee)

MA X7.IC.A Moisture Analyzer
 MA 5Y Moisture Analyzer
 AS X7 Analytical Balance

MA 5Y.IC Moisture Analyzer
 MA R Moisture Analyzer
 PS R2.H Precision Balance

PS R2 Precision Balance
WLC X7 Precision balance
C32.PM Precision Balance
MA X7.A Moisture Analyzer
PS X7 Precision Balance

Analytical Balance for Filters XA 5Y.F
PS R1 Precision Balance
AS R2 PLUS Analytical Balance
MAS1 Modules
AS R1 PLUS Analytical Balance

Device dimensions W x D x H

