



More information on the website
mirror.radwag.com/en/info,w1,KZVYM

AKM-2.50.5Y Automatic Mass Comparators

WL-411-0014



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
E1 Calibration Range	20 – 50 kg
E2 Calibration Range	5 – 50 kg
F1 Calibration Range	5 – 50 kg
F2 Calibration Range	5 – 50 kg
M1 Calibration Range	-
M2 Calibration Range	-
Maximum capacity [Max]	51 kg
Readability [d]	1 mg
Standard repeatability [Max]	2 mg
Permissible repeatability	3 mg
Eccentricity (tested load)	0 mg
Electric compensation range	0 g – +51 kg
Stabilization time	30 s
Adjustment	external

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	ø100 mm
Weighing device dimensions	1050×650×1150 mm
Controlling device dimensions	249×170×72 mm
Packaging dimensions	1770×900×1100 mm
Net weight	260 kg
Net weight	260 kg
Gross weight	380 kg
Gross weight	380 kg
Supplementary weights internal	-
Supplementary weights external	-
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0.5 °C / 12 h (±0.3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (3% / 4 h)

Repeatability is expressed as a standard deviation determined for 6 ABBA cycles. Standard deviation is experimentally determined under ambient conditions for calibration of E1 class mass standards specified in OIML R111 (Table C.1.) document.

E0 standard determined from 1/5 limiting error according to OIML R111 for class E1

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.





Accessories (Additional Fee)

RFID Tags	THBR 2.0 System - Ambient Conditions Monitoring
Additional modules	Receipt Printer
Protective cover for balances	Fingerprint Reader
Barcode scanners	RS 232, RS 485 cables
RS 232, RS 485 cables	RS 232 cables (scale - printer)

Software (Additional Fee)

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]
- RMCS Lite [WX-010-0164]

Device dimensions



AKM-2