



More information on the website  
[mirror.radwag.com/us/info,w1,L6U](https://mirror.radwag.com/us/info,w1,L6U)

# Módulo de pesagem MPS.M.5100/10000.Y

WX-016-1004



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	5100 / 10000 g
Preload range	1 kg
Readability [d]	0,01 / 0,05 g
Repeatability	0,01 / 0,05 g
Linearity	±20 / 50 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	internal
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	
Communication interface	RS232, Ethernet TCP/IP

<b>Communication interface</b>	
Optional interfaces	RS485, 2 IN/2 OUT
<b>Electrical parameters</b>	
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC
<b>Environmental conditions</b>	
Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
<b>Physical parameters</b>	
Weighing pan dimensions	ø100 mm
Device dimensions W x D x H	266x70x105 mm
Net weight	1,8 kg



# Device dimensions W x D x H

