



More information on the website
mirror.radwag.com/us/info,w1,L6U

Módulo de pesagem MPS.M.5100/10000.Y

WX-016-1004



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	5100 / 10000 g
Preload range	1 kg
Readability [d]	0,01 / 0,05 g
Repeatability	0,01 / 0,05 g
Linearity	±20 / 50 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	internal
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	RS232, Ethernet TCP/IP
Optional interfaces	RS485, 2 IN/2 OUT

Power supply

Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC

Operating temperature

+10 – +40 °C

Relative humidity

40% – 80%

Physical parameters

Weighing pan dimensions

Ø100 mm

Device dimensions W x D x H

266x70x105 mm

Net weight

1,8 kg



Device dimensions W x D x H

