



# CY10.15.C3.K.M3 Multifunctional Scale

WP-125-0037

More information on the website  
[mirror.radwag.com/us/info,w1,M4C](http://mirror.radwag.com/us/info,w1,M4C)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

## Datasheet

| Metrological parameters                |        |
|--|--------|
| Maximum capacity [Max]                 | 15 kg  |
| Minimum load                           | 10 g   |
| Readability [d]                        | 5 g    |
| Verification unit [e]                  | 5 g    |
| Tare range                             | -15 kg |
| Max readability for non-verified scale | 0,5 g  |
| Stabilization time                     | 3 s    |

| Metrological parameters        |  |
|--------------------------------|--|
| Adjustment                     | external   |
| OIML Class                     | III  |
| Physical parameters            |  |
| Leveling system                | manual   |
| Display                        | 10" graphic colour touchscreen   |
| Cable length                   | 2,5 m  |
| Weighing pan dimensions        | 500×700 mm   |
| Packaging dimensions W x D x H | 850×800×270 mm   |
| Net weight                     | 22,7 kg  |
| Gross weight                   | 26,5 kg  |
| Construction                   |  |
| Protection class               | IP 65 construction, IP 43 terminal   |
| Housing                        | steel + ABS  |
| Communication interface        |  |
| Communication interface        | 2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot                            |
| Electrical parameters          |  |
| Power supply                   | Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A<br>Balance: 12 – 15V DC 1,6A max; 10–19W* |
| Environmental conditions       |  |
| Operating temperature          | -10 – +40 °C   |
| Storage temperature            | -25 – +70 °C   |
| Multiple range                 | YES  |
| Features of use                |  |
| Max number of platforms        | max.2  |

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



## Accessories (Additional Fee)

### MediaBox

Mild steel powder coated weighing platforms  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module  
Additional modules  
Platforms in plastic casing  
Protective cover for balances

### Barcode scanners

Label Printers  
RS 232, RS 485 cables  
Stands, wall mounting kits and mounting brackets  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions W x D x H

