



More information on the website  
[mirror.radwag.com/us/info,w1,MGI](https://mirror.radwag.com/us/info,w1,MGI)

# H315.60/150.HR3/5.M Waterproof Scale With Stainless Steel Load Cell

WP-124-1071



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit  
 measurement



Animal weighing

## Datasheet

| Maximum capacity [Max]  | 60 / 150 kg        |
|-------------------------|--------------------|
| Minimum load            | 400 g              |
| Readability [d]         | 20 / 50 g          |
| Verification unit [e]   | 20 / 50 g          |
| Tare range              | -150 kg            |
| OIML Class              | III                |
| Physical parameters     |                    |
| Display                 | 4,3" LCD (backlit) |
| Weighing pan dimensions | 400×600 mm         |

| Physical parameters            |                                                                         |
|--------------------------------|-------------------------------------------------------------------------|
| Packaging dimensions W x D x H | 710×510×330 mm                                                          |
| Net weight                     | 15,5 kg                                                                 |
| Gross weight                   | 17,3 kg                                                                 |
| Construction                   |                                                                         |
| Protection class               | IP 66 / 67 / 69 construction, IP 68 / 69 cell, IP 66 / 67 / 69 terminal |
| Construction                   | Stainless steel AISI316                                                 |
|                                |                                                                         |
| Communication interface        | RS232, USB                                                              |
| Optional interfaces            | RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA         |
|                                |                                                                         |
| Power supply                   | 100 – 240 V AC 50/60 Hz                                                 |
| Optional power supply          | internal rechargeable battery                                           |
| Operation time on batteries    | max 7h                                                                  |
|                                |                                                                         |
| Operating temperature          | -10 – +40 °C                                                            |
| Storage temperature            | -25 – +70 °C                                                            |
| Relative humidity              | 10% – 85% RH no condensation                                            |



Additional fee for verification



## Accessories (Additional Fee)

AP2-3 Current Loop Unit  
 RS 232 cables (scale - printer)  
 Antivibration tables  
 Displays  
 Ethernet cables (scale - Ethernet)  
 RS 232, RS 485 cables  
 Power Adapters


RS 232 – Ethernet Converter  
 USB adapter  
 Receipt Printer  
 USB cable (scale - printer)  
 Stands, wall mounting kits and mounting brackets  
 RS 232 – USB Converter  
 Roller table

## Software (Additional Fee)

• RAD Key [WX-010-0005]

• Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions W x D x H



|                |           | A1  | A2  | B           | C1  | C2  | D    | E    | L    |
|----------------|-----------|-----|-----|-------------|-----|-----|------|------|------|
| H315...HR2.M   | 250 x 300 | 246 | 306 | $104 \pm 3$ | 208 | 268 | ~525 | ~483 |      |
| H315...HR2.K   | 250 x 300 | 246 | 306 | $104 \pm 3$ | 208 | 268 | -    | -    | 1,5m |
| H315...HR3.M   | 410 x 410 | 410 | 410 | $98 \pm 2$  | 370 | 370 | ~525 | ~587 |      |
| H315...HR3.K   | 410 x 410 | 410 | 410 | $98 \pm 2$  | 370 | 370 | -    | -    | 2,5m |
| H315...HR4.M   | 500 x 500 | 497 | 497 | $155 \pm 5$ | 400 | 400 | ~767 | ~650 |      |
| H315...HR4.K   | 500 x 500 | 497 | 497 | $155 \pm 5$ | 400 | 400 | -    | -    | 2,5m |
| H315...HR3/5.M | 400 x 600 | 597 | 397 | $155 \pm 5$ | 500 | 300 | ~767 | ~550 |      |
| H315...HR3/5.K | 400 x 600 | 597 | 397 | $155 \pm 5$ | 500 | 300 | -    | -    | 2,5m |
| H315...HR5.M   | 600 x 600 | 597 | 597 | $155 \pm 5$ | 500 | 500 | ~767 | ~750 |      |
| H315...HR5.K   | 600 x 600 | 597 | 597 | $155 \pm 5$ | 500 | 500 | -    | -    | 2,5m |