



More information on the website
mirror.radwag.com/us/info,w1,MLL

APP 10.5Y.KO Mass Comparator

WL-407-0036



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|---------------------------------|----------------------|
| E1 Calibration Range | 5 – 10 kg |
| E2 Calibration Range | 1 – 10 kg |
| F1 Calibration Range | 500 g – 10 kg |
| F2 Calibration Range | 100 g – 10 kg |
| M1 Calibration Range | 100 g – 10 kg |
| M2 Calibration Range | 100 g – 10 kg |
| Maximum capacity [Max] | 10,2 kg |
| Readability [d] | 0,1 mg |
| Standard repeatability [5% Max] | 0,35 mg |
| Standard repeatability [Max] | 0,4 mg |
| Permissible repeatability | 0,7 mg |
| Linearity | ±0,6 mg |
| Eccentricity (tested load) | 2d / 1 mm |
| Electric compensation range | -100 g – +200 g |
| Stabilization time | 30 s |
| Adjustment | internal (automatic) |

| Physical parameters | |
|-----------------------------------|---|
| Display | 10" graphic colour touchscreen |
| Weighing pan dimensions | ∅190 (∅300) mm |
| Weighing device dimensions | 455×300×380 mm |
| Controlling device dimensions | 249×170×72 mm |
| Packaging dimensions W x D x H | 1160×650×700 mm |
| Chamber packaging size | 960×920×735 mm |
| Net weight | 46 kg |
| Gross weight | 60 kg |
| Construction | |
| Supplementary weights | internal (automatic) |
| Supplementary weights internal | half automatic |
| Supplementary weights external | 300 g, 200 g |
| Communication interface | 2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot |
| Operating temperature | +15 – +30 °C |
| Operating temperature change rate | ±0,5 °C / 12 h (±0,3 °C / 1 h) |
| Relative humidity | 40% – 60% |
| Relative humidity change rate | ±5% / 4 h |

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

Self-centering pan for APP KO comparator
 RFID Tags
 Antivibration tables
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables

Label Printers
 THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 Anti-Draft Chamber for Mass Comparators
 RS 232 cables (scale - printer)

Software (Additional Fee)

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]

Device dimensions W x D x H

