



# DWM HPE Dynamische Etikettenwaage

WK-105-0000

More information on the website  
[mirror.radwag.com/de/info,w1,MR6](http://mirror.radwag.com/de/info,w1,MR6)



The drawings, photos and graphics used are for illustrative purposes only.

## Technische Daten

Messtechnische Parameter	
Wägebereich [Max]	3000 – 7500 g
Zifferschritt [d]	1 – 5 g
OIML-Klasse	XIII (1), Y (a)
Physikalische Parameter	
Display	12" grafisch farbiger Touchscreen
Labelling throughput	60 St./min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106 / 162,6 mm
Label width	114 / 174 mm
Roller external diameter	305 mm
Print method	Thermisch / Thermotransfer
Kommunikationsschnittstellen	
Schnittstellen	Ethernet, USB, RS232, I / O

## Konstruktion

Konstruktion pulverbeschichteter Stahl / Edelstahl

Wägesystem elektromagnetischer Modul



## Zubehör (Additional Fee)

Thermische Drucker