



DWM HPE Dynamische Etikettenwaage

WK-105-004_

More information on the website
mirror.radwag.com/de/info,w1,MR6



The drawings, photos and graphics used are for illustrative purposes only.

Technische Daten

Messtechnische Parameter	
Wägebereich [Max]	3000 – 7500 g
Ablesbarkeit [d]	1 – 5 g
OIML-Klasse	XIII (1), Y (a)
Physikalische Parameter	
Display	12" grafisch farbiger Touchscreen
Labelling throughput	60 St./min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106 / 162,6 mm
Label width	114 / 174 mm
Roller external diameter	305 mm
Print method	Thermisch / Thermotransfer
Kommunikationsschnittstellen	
Schnittstellen	Ethernet, USB, RS232, I / O

Konstruktion

Konstruktion pulverbeschichteter Stahl / Edelstahl

Wägesystem elektromagnetischer Modul

Komponenten und Software

Betriebssystem Microsoft Windows 11 IoT



Zubehör (Additional Fee)

Thermische Drucker