



DWM HPE Labelling Checkweigher

WK-105-0000

More information on the website
mirror.radwag.com/en/info,w1,MR6



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	3000 – 7500 g
Readability [d]	1 – 5 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Labelling throughput	60 pcs/min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106 / 162.6 mm
Label width	114 / 174 mm
Roller external diameter	305 mm
Print method	thermal / thermal transfer
Communication interface	
Communication interface	Ethernet, USB, RS232, I / O

Construction

Construction	mild steel / Stainless steel
Weighing module	electromagnetic weighing module

Components and software

Operating system	Microsoft Windows 11 IoT
------------------	--------------------------



Accessories (Additional Fee)

Receipt Printer