



# DWM HPE Labelling Checkweigher

WK-105-004\_

More information on the website  
[mirror.radwag.com/en/info,w1,MR6](http://mirror.radwag.com/en/info,w1,MR6)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                                |
|--------------------------|--------------------------------|
| Maximum capacity [Max]   | 3000 – 7500 g                  |
| Readability [d]          | 1 – 5 g                        |
| OIML Class               | XIII (1), Y (a)                |
| Physical parameters      |                                |
| Display                  | 12" graphic colour touchscreen |
| Labelling throughput     | 60 pcs/min                     |
| Print resolution         | 300/600 dpi                    |
| Print speed              | max 300 mm/s                   |
| Print width              | 106 / 162.6 mm                 |
| Label width              | 114 / 174 mm                   |
| Roller external diameter | 305 mm                         |
| Print method             | thermal / thermal transfer     |
| Communication interface  |                                |
| Communication interface  | Ethernet, USB, RS232, I / O    |

### Construction

|                 |                                 |
|-----------------|---------------------------------|
| Construction    | mild steel / Stainless steel    |
| Weighing module | electromagnetic weighing module |

### Components and software

|                  |                          |
|------------------|--------------------------|
| Operating system | Microsoft Windows 11 IoT |
|------------------|--------------------------|



## Accessories (Additional Fee)

Receipt Printer