



More information on the website
mirror.radwag.com/it/info,w1,MR6

Bilancia di etichettatura dinamica DWM HPE

WK-105-004_



The drawings, photos and graphics used are for illustrative purposes only.

Specifiche

Parametri metrologici

Portata massima [Max]	3000 – 7500 g
Divisione [d]	1 – 5 g
Classe OIML	XIII (1), Y (a)

Parametri fisici

Display	12" graphic colour touchscreen
Labelling throughput	60 pcs/min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106 / 162,6 mm
Label width	114 / 174 mm
Roller external diameter	305 mm
Print method	thermal / thermal transfer

Interfaccia di comunicazione

Interfaccia	Ethernet, USB, RS232, I / O
-------------	-----------------------------

Costruzione

Costruzione	mild steel / Stainless steel
Modulo di pesata	electromagnetic weighing module

Components and software

Sistema operativo	Microsoft Windows 11 IoT
-------------------	--------------------------



Accessori (Additional Fee)

Stampanti di ricevuta