



# DWM HPE Labelling Checkweigher

WK-105-004\_

More information on the website  
[mirror.radwag.com/us/info,w1,MR6](http://mirror.radwag.com/us/info,w1,MR6)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	3000 – 7500 g
Readability [d]	1 – 5 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Labelling throughput	60 pcs/min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106 / 162,6 mm
Label width	114 / 174 mm
Roller external diameter	305 mm
Print method	thermal / thermal transfer
Communication interface	
Communication interface	Ethernet, USB, RS232, I / O

### Construction

Construction	mild steel / Stainless steel
Weighing module	electromagnetic weighing module

### Components and software

Operating system	Microsoft Windows 11 IoT
------------------	--------------------------



## Accessories (Additional Fee)

Receipt Printer