



More information on the website  
[mirror.radwag.com/de/info,w1,MVB](http://mirror.radwag.com/de/info,w1,MVB)

# Palettenwaage C315.4P.3000.C


WP-239-0002




The drawings, photos and graphics used are for illustrative purposes only.

## Funktionen

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

## Technische Daten

Messtechnische Parameter	
Wägebereich [Max]	3000 kg
Min. Belastung	20 kg
Ablesbarkeit [d]	1000 g
Tarierbereich	-3000 kg
Max Ablesbarkeit [d] bei nicht geeichter Waage	1000 g
OIML-Klasse	III

Physikalische Parameter	
Display	4,3" LCD (hinterleuchtet)
Kabellänge	3 m
Waagschale	840×1200 mm
Abmessungen des Geräts B x T x H	1322×840×85 mm
Verpackungsgröße B x T x H	1400×900×430 mm
Gewicht der Waage mit Messgerät	43 kg
Konstruktion	
Schutzart	IP 65 Konstruktion, IP 67 Tensometer, IP 43 Terminal
Kommunikationsschnittstellen	
Schnittstellen	RS232
Optionale Schnittstellen	RS232
Elektrische Parameter	
Stromversorgung	100 – 240 V AC 50/60 Hz + Akkus
Maximaler Leistungsaufnahme	5 W
Akku-Betriebszeit	max 8h
Umgebungsbedingungen	
Umgebungstemperatur	-10 – +40 °C
Relative Luftfeuchtigkeit	10% – 85% RH ohne Kondensation



Additional fee for verification



## Zubehör (Additional Fee)

### Netzteile

Kabel RS 232 (Waage – Drucker)

Wandhalterung, Stativ

Anschlusskabel für Zigarettenanzünder

Displays

Kabel RS 232, RS 485

Konverter RS 232 – Ethernet

Ausgang der Stromschnittstelle AP2-1

Konverter RS 232 – USB

Konverter RS 232 – RS 485

Thermische Drucker

## Software (Additional Fee)




• RAD Key [WX-010-0005]

• RLAB [WX-010-0080]

• R Panel [WX-010-0187]

• Scale Editor 2.1 [WX-010-0173]

# Abmessungen des Geräts B x T x H



Warunki transportu i przemieszczania wagi paletowej przy pomocy kółek jezdnych oraz uchwytów.

Transport of the pallet scale using casters and handles.