



Multi-Track DWM H2 Checkweigher

WK-105-00_

More information on the website
mirror.radwag.com/en/info,w1,MWB



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 – 7500 g
Minimum load	4 – 20 g
Readability [d]	0.2 – 1 g
Verification unit [e]	0.2 – 1 g
Tare range	-1500 – -7500 g
Max readability for non-verified scale	0.2 – 1 g
Expanded reading unit	0.01 – 0.5 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	mild steel / Stainless steel

Communication interface	
Communication interface	Ethernet, USB, RS232, I / O, Modbus, ProfiNet (option), ProfiBus (option)
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+5 – +40 °C
Components and software	
Operating system	Microsoft Windows 11 IoT
Features of use	
Conveyor velocity	1.6 m/s



Accessories (Additional Fee)

RS 232 cables (scale - ZEBRA printer)
 RS 232, RS 485 cables
 Tunnel Detectors
 Keypad, external switches

USB adapter
 Receipt Printer
 USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]