



Multi-Track DWM H2 Checkweigher

WK-105-005_

More information on the website
mirror.radwag.com/us/info,w1,MWB



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	750 – 7500 g
Readability [d]	0,1 – 5 g
Verification unit [e]	0,1 – 5 g
Max readability for non-verified scale	0,2 – 1 g
Expanded reading unit	0,01 – 0,5 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	Stainless steel
Communication interface	
Communication interface	RS232, USB, Ethernet, IN/OUT

Communication interface	
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+5 – +40 °C
Components and software	
Operating system	Microsoft Windows 11 IoT
Features of use	
Capacity	max 2 x 500 pcs/min
Conveyor velocity	1,6 m/s



Accessories (Additional Fee)

RS 232 cables (scale - ZEBRA printer)
 RS 232, RS 485 cables
 Tunnel detectors
 Keypad, external switches

USB adapter
 Receipt Printer
 USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]