



More information on the website
mirror.radwag.com/us/info,w1,N0J
























XA 52.5Y.A Analytical Balance

WL-110-0001



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	52 g
Minimum load	1 mg

Metrological parameters	
Readability [d]	0,01 mg
Verification unit [e]	1 mg
Tare range	-52 g
Minimum weight (USP)	10 mg
Minimum weight (U=1%, k=2)	1 mg
Standard repeatability [5% Max]	0,005 mg
Permissible repeatability [5% Max]	0,012 mg
Linearity	±0,03 mg
Eccentric load deviation	0,03 mg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times \text{Rt}$
Stabilization time	4 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Weighing chamber doors	automatic
Delivery components	Analytical Balance, weighing pan, weighing pan shield, centring ring, brush, fabric dust cover, power supply.
Weighing chamber dimensions	200×170×220 mm
Weighing pan dimensions	∅90 open-work pan + ∅85 (option) mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	15,5 kg
Gross weight	20 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10 – 19W*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	20% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories (Additional Fee)

MediaBox
 RFID Tags
 Antivibration tables
 Adapters for pipettes calibration
 Power Adapters
 Protective cover for balances
 RS 232, RS 485 cables
 Density determination KIT
 Additional modules
 Professional Weighing Tables
 Barcode scanners
 Automatic feeders

Label Printers
 THBR 2.0 System - Ambient Conditions Monitoring
 MICRO-KIT - Set of Holders for Microscale Glassware
 Under-pan weighing
 Anti-Draft Chamber for XA 4Y and XA 5Y Balances
 Weighing dishes
 Antistatic ionizer
 Receipt Printer
 Fingerprint Reader
 Adapter for Pipettes Calibration
 RS 232 – USB Converter
 !Balance Storage Case

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

