



More information on the website  
[mirror.radwag.com/us/info,w1,N7C](http://mirror.radwag.com/us/info,w1,N7C)

# Módulo de pesagem MPS.M.3300.R2

WX-016-0336



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	3300 g
Preload range	330 g
Readability [d]	10 mg
Repeatability	7 mg
Linearity	±20 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	internal
<b>Construction</b>	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	RS232, max 115,2 kbps, Radwag ASCII protocol
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC

Operating temperature	+10 – +40 °C
-----------------------	--------------

Relative humidity	40% – 80%
-------------------	-----------

#### Physical parameters

Weighing pan dimensions	ø100 mm
-------------------------	---------

Device dimensions W x D x H	266x70x105 mm
-----------------------------	---------------

Net weight	1,8 kg
------------	--------



## Accessories (Additional Fee)

RS 232, RS 485 cables

## Software (Additional Fee)

• R Panel [WX-010-0187]

# Device dimensions W x D x H

