



More information on the website
mirror.radwag.com/us/info,w1,N7C

Módulo de pesagem MPS.M.3300.R2

WX-016-0336



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	3300 g
Preload range	330 g
Readability [d]	10 mg
Repeatability	7 mg
Linearity	±20 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	internal
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	RS232, max 115,2 kbps, Radwag ASCII protocol
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC

Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
Physical parameters	
Weighing pan dimensions	ø100 mm
Device dimensions W x D x H	266x70x105 mm
Net weight	1,8 kg



Accessories (Additional Fee)

RS 232, RS 485 cables
Antivibration tables

R Terminal (WDM-8)

Software (Additional Fee)

• R Panel [WX-010-0187]

Device dimensions W x D x H

