



AS 60/220.5Y Analytical Balance

WL-104-0529

More information on the website
mirror.radwag.com/en/info,w1,NC3



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	60 / 220 g
Minimum load	1 mg

Metrological parameters	
Readability [d]	0.01 / 0.1 mg
Verification unit [e]	1 mg
Tare range	-220 g
Minimum weight (USP)	20 mg
Minimum weight (U=1%, k=2)	2 mg
Standard repeatability [Max]	0.06 mg
Standard repeatability [5% Max]	0.01 mg
Permissible repeatability [Max]	0.1 mg
Permissible repeatability [5% Max]	0.02 mg
Linearity	±0.05 / 0.2 mg
Stabilization time	2 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Balance, weighing pan, weighing pan shield, centring ring, bottom cover, power supply, fabric dust cover.
Weighing chamber dimensions	190×190×227 mm
Weighing pan dimensions	ø90 open-work pan + ø85 (option) mm
Packaging dimensions W x D x H	600×400×550 mm
Net weight	7.14 kg
Gross weight	10.5 kg
Construction	
Protection class	IP 43
Components and software	
Database capacity	7
Features of use	
Touch-free operation	2 IR Sensors
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max; 9 – 17W*
Environmental conditions	
Operating temperature	+10 – +40 °C
Ambient conditions monitoring (option)	THBR 2.0 System, THBR BOX, THB P, THB W, THB S
Relative humidity	40% – 80%

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

¹ Barcode scanners, available as weighing instrument accessory, communicate with the instrument via USB interface exclusively.
* Power consumption depends on the terminal configuration and the number and type of external devices connected.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

Antivibration Tables
Holders for laboratory flasks
Power Adapters
RS 232, RS 485 cables
Cigarette lighter receptacle power supply cables
Density determination KIT
Additional modules
Protective cover for balances
USB cable (scale - printer)
Professional Weighing Tables
Barcode scanners

Holders for test tubes and filters
Workstation for Pipettes Calibration
THBR 2.0 System - Ambient Conditions Monitoring
Weighing dishes
Antistatic ionizer
Receipt Printer
Fingerprint Reader
Under-pan weighing
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions W x D x H

