



More information on the website
mirror.radwag.com/us/info,w1,NEV

AP-12/12.5Y Automatic Device for Multichannel Pipette Calibration

WL-101-0429



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Statistics



IR sensors



GLP Procedures



Pipettes Calibration



Air density correction



Ambient conditions monitoring



Statistical Quality Control



ALIBI Memory

Datasheet

Maximum capacity [Max]	25 g (per measuring channel)
Readability [d]	0,01 mg
Standard repeatability [Max]	10 µg
Standard repeatability [5% Max]	5 µg
Linearity	±0,03 mg
Stabilization time	4 s
Adjustment	internal (automatic), external

Typical measurement time for a 12-channel pipette with constant volume, according to ISO 8655 (for d=10 µg)*	5 min
Typical measurement time for a 12-channel pipette with variable volume, according to ISO 8655 (for d=10µg)*	15 min
Maximum volume of dishes	16 ml (per measuring channel)
Physical parameters	
Display	10" graphic colour touchscreen
Delivery components	pipette calibration balance, terminal, transport case, liquid suction pump, vapor curtain
Weighing pan dimensions	intended
Device dimensions W x D x H	563x393x214
Packaging dimensions W x D x H	490x700x700 mm
Net weight	30 kg
Gross weight	40 kg
Communication interface	2xUSB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2,4A Device: 12 – 15V DC 1,6A max; 10 – 29W*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	20% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

Antivibration tables
Additional modules
Automatic Variable-Volume Pipettes
Weighing Tables
Protective cover for balances
Barcode scanners

!Balance Storage Case
RS 232, RS 485 cables
Suction pumps for liquids
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter

Software (Additional Fee)

- RAD Key [WX-010-0005]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

