



More information on the website  
[mirror.radwag.com/us/info,w1,NII](http://mirror.radwag.com/us/info,w1,NII)

# DWM HPS Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	1500 – 6000 g
Minimum load	20 – 100 g
Readability [d]	0,5 – 2 g
Tare range	-1500 – -6000 g
<b>Physical parameters</b>	
Display	12" graphic colour touchscreen
<b>Construction</b>	
Protection class	IP 65
Construction	Stainless steel AISI304
Max. dimensions of sorted product [length x width]	350x180 - 500x280 mm
Weighing module	electromagnetic weighing module
Conveyors	belt
Pneumatic connector	6 bar quick coupling intended for 12 mm cable
Communication interface	Ethernet, USB, RS232, I / O

Power supply	100 – 240 V AC 50/60 Hz
--------------	-------------------------

#### Features of use

Conveyor velocity	1,6 – 1 m/s
-------------------	-------------

Number of separators	6 or 12
----------------------	---------



## Accessories

Receipt Printer

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]